





REV.	REVISION DESCRIPTION	DATE	APPD

技术要求 (Technical requirements) :

- 1. 材质 (material): 黄铜 (brass)
- 2. 材料规格 (Material specifications) : 0.35mm
- 3. 压线范围 (Wire) : AWG24#--14#
- 4. 表面处理 (Surface treatment) : 锡 (Tin plated)
- 5. 额定电压 Rated voltage : 300V AC.DC.
- 6. 额定电流 Rated current : 15A AC.DC.
- 7. 接触电阻 Contact resistance: 20mΩ MAX
- 8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
- 9. 耐压 Withstand voltage: 2000V AC/minute
- 10. 配 0.5/0.8mm 插片


Product name	Dimension mm			
	A1	B1	A2	B2
DL187ZCDJ	4.0	4.4	2.3	2.8
DL187ZCZJ	4.75	4.9	3.0	3.0
DL187ZCGJ	5.5	5.7	3.8	3.8


GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司			
		ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.25	. X° : ±3.0°	PRODUCT NAME:		TITLE:	
. XX: ±0.15	. XX° : ±2.0°	DL187ZCxx		187	
. XXX: ±0.01	. XXX° : ±1.0°	DR. :Chen Quan Long	DATE. :21.04.11	PART. NO. :	
FINISH:		CHKD. :Wu Hui	DATE. :21.04.11	SCALE: N/A	PAGE: 1/1
DRAWING NO. :		APPD. :Ren An De	DATE. :21.04.11	UNITS: mm	REV. : A



Product name	Dimension mm				Applicable wires
	A1	B1	A2	B2	AWG#
DL187ZCDSJ	4.5	4.5	2.7	2.3	22-18
DL187ZCDSZJ	5.0	5.2	3.2	3.4	18-16
DL187ZCDSGJ	5.4	5.4	3.6	4.0	16-14

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司			
. X: ±0.25	. X°: ±3.0°	ZHEJIANG DELI CONNECTORS CO.,LTD		PRODUCT NAME: DL187ZCDSxx	
. XX: ±0.15	. XX°: ±2.0°	TITLE: 187		PART. NO.:	
. XXX: ±0.01	. XXX°: ±1.0°	DR.: Chen Quan Long	DATE.: 21.04.11	SCALE: N/A	
FINISH:		CHKD.: Wu Hui	DATE.: 21.04.11	PAGE: 1/1	
DRAWING NO.:		APPD.: Ren An De	DATE.: 21.04.11	UNITS: mm	REV.: A









技术要求 (Technical requirements) :


1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.35mm
3. 压线范围 (Wire) : AWG20#--14#
4. 表面处理 (Surface treatment) : 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.5 X° : ±3.0°		PRODUCT NAME: DL187QX		TITLE: 187	
. XX: ±0.35 . X° : ±2.0°		DR.:Zhang Wen Jing DATE.:10.04.1		PART. NO.:	
. XXX: ±0.10 . XX° : ±1.0°		CHKD.:Liu Bing DATE.:10.04.1		SCALE: N/A PAGE: 1/1	
FINISH: _____		APPD.:Ren An De DATE.:10.04.1		UNITS: mm REV. : A	
					
DRAWING NO.:					





技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.3mm
3. 压线范围 (Wire) : AWG18#--14#
4. 表面处理 (Surface treatment) : 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 10mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配 0.5/0.8mm 插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL187QXDS		TITLE: 187	
.XX: ±0.15	.X° : ±2.0°				
.XXX: ±0.01	.XX° : ±1.0°	DR. :Chen Quan Long	DATE. :20.04.1	PART NO. : SCALE: N/A	
FINISH: 	CHKD. :Wu Hui	DATE. :20.04.1	PAGE: 1/1		
DRAWING NO. :		APPD. :Ren An De	DATE. :20.04.1	UNITS: mm	REV. : A

REV.	ECN. NO.	REVISION DESCRIPTION	DATE	APPD







技术参数 (SPECIFICATIONS)

- 额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 15A
接触电阻 (Contact resistance): ≤0.02Ω
绝缘电阻 Insulation resistance: 1000 MΩ MIN
耐压 Withstand voltage: 1500V AC/minute
材质 (material): 黄铜 (brass)
材料规格 (Material specifications): 0.8mm
表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)



GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	.X°: ±3.0°	PRODUCT NAME: DL1870122ST0.8		TITLE: 187	
.XX: ±0.15	.XX°: ±2.0°	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
.XXX: ±0.01	.XXX°: ±1.0°	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					



技术参数 (SPECIFICATIONS)

- 额定电压 (Voltage rating): 300V, AC, DC
- 额定电流 (Current rating): 15A
- 接触电阻 (Contact resistance): $\leq 0.02 \Omega$
- 绝缘电阻 (Insulation resistance): 1000 M Ω MIN
- 耐压 (Withstand voltage): 2000V AC/minute
- 材质 (material): 黄铜 (brass)
- 材料规格 (Material specifications): 0.5mm
- 表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	.X°: ±3.0°	PRODUCT NAME: DL1870222ST0.5		TITLE: 187	
.XX: ±0.15	.XX°: ±2.0°	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
.XXX: ±0.01	.XXX°: ±1.0°	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					



技术参数 (SPECIFICATIONS)

额定电压 (Voltage rating): 300V, AC, DC

额定电流 (Current rating): 15A

接触电阻 (Contact resistance): $\leq 0.02 \Omega$

绝缘电阻 Insulation resistance: 1000 M Ω MIN

耐压 Withstand voltage: 2000V AC/minute

材质 (material): 黄铜 (brass)

材料规格 (Material specifications): 0.8mm

表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	.X°: $\pm 3.0^\circ$	PRODUCT NAME: DL1870222ST0.8		TITLE: 187	
.XX: ± 0.15	.XX°: $\pm 2.0^\circ$	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
.XXX: ± 0.01	.XXX°: $\pm 1.0^\circ$	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					