



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA66 BLACK

b.CONTACT:SUS304 T=0.4MM

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-26650-A1BJ002

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING




MATERIAL:

1B-PA66 BLACK

工程部

2025-04-24

H. WANG



PCB Layout Diagram

TOP View

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2025-04-24	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-04-24	电池盒BH-26650-1J Ni DIP PA66	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyang	DATE	2025-04-24	PART NO.:	
X.XX :±0.20		WEIGHT:		SCALE: 1:1	SIZE: A4	BH-26650-A1BJ002	
X.XXX :±0.10		SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	DRAW NO.:WD-CP-0476

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
2	TERMINAL	2	SUS304, T=0.4MM	Ni-Plating
1	HOUSING	1	PA66	BLACK