



7		8	
REV.	ECN NO.	REVISED	DATE

OTE:

1.MATERIAL:

a.HOUSING: PPA OFF WHITE

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Au 1u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25° C~ +85° C

ORDERING INFORMATION

BS-08-B2CA042

电池座

电池型号

SMT 180° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

2C-PPA WHITE

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE






4B-LCP BLACK

5A-PA9T BLACK


工程部

2024-03-04

LQ. HUANG



PCB Layout Diagram
Bottom View



NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL-	1	PHOSPHOR BRONZE, T=0.2mm	Au-Plating
2	TERMINAL+	1	PHOSPHOR BRONZE, T=0.2mm	Au-Plating
1	HOUSING	1	PPA	WHITE

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2024-03-04
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-03-04
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2024-03-04
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE:	
				BS-2032-8-2 Au SMT PPA白色	
				PART NO.:	
				BS-08-B2CA042	
				DRAW NO.:MY-CP-0395	