



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000mΩ
- 6、Withstanding Voltang: 1500V AC,
- 7、Material:Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	
3.96-2A	3.96	
3.96-3A	7.92	
3.96-4A	11.88	
3.96-5A	15.84	
3.96-6A	19.80	
3.96-7A	23.76	
3.96-8A	27.72	
3.96-9A	31.68	
3.96-10A	35.64	
3.96-11A	39.60	
3.96-12A	43.56	
3.96-15A	55.44	

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图		料 号		片	
			X.±0.25	X.°±2°			PART NO.		3.96直针座	REV
							品 名			页
			Y.±0.20		审 核		TITLE		SHEET	
			Y.°±1°				客户料号			