

REV.	MATERIAL	APP.	DATE
A			

ø20.10

ø22.10




24.50

7.50

③

②

①



- NOTE:
1. MATERIAL:  
a. HOUSING: THERMOPLASTIC GLASS FIBRE UL94V-0  
b. CONTACT: Phosphor bronze  
c. Plating: SN100~120U",
2. ELECTRIC:  
a. CONTACT RESISTANCE: 50 MILLIOHMS MAX  
b. INSULATION RESISTANCE: 100 MEGA OHMS MIN  
c. DIELECTRIC VOLTAGE: 550V AC ONE SEC LEVEL  
d. OPERATING TEMPERATURE: -55~C ~ +85~C

### ORDERING INFORMATION


BS-02-A\*\*0\*003

電池座系列  
BS-2系列  
DIP 90 TYPE

MATERIAL:  
1A-PBT WHITE  
1B-PBT BLACK  
3A-PBT WHITE  
3B-PBT BLACK

PLATING:  
J-SN100~120U  
K-Sn 5um  
M-Ni 2um~3um

CRUST:  
0-WITHOUT



深圳市琦捷电子有限公司

TOLERANCE	DRAWN	ANGLE	UNIT:	TITLE:
$x \pm 0.38$	李杰	$x^{\circ} \pm 5^{\circ}$	MM	阻燃电池座QJ (BS-2-1)
$xx \pm 0.25$	APPROVED	$xx^{\circ} \pm 2^{\circ}$	PART NO.	BS-02-A1BJ003
$xxx \pm 0.10$	DATE	$xxx^{\circ} \pm 1^{\circ}$	SCALE:	REV. A
	2024.06.10		SIZE: A4	QJ-B5-2-1 (3.6)
			SHEET:	1 OF 1