


焊接图



电路图

主要技术规格:




1. 额定值: 50mA DC12V
2. 接触电阻: 100mΩ (初期值)
3. 操作力: 250±50gf
4. 行程: 0.25±0.1mm
5. 绝缘电阻: 100MΩ
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 10万 Cycles

材料:

本体:PPA (黑色)
按钮:PPA (黑色)
卡件: 黄铜 (镀银)
弹片: 不锈钢 (镀银)
盖板: 铁 (镀锡)




标记	处数	更改文件号	签名	日期	比例		一般公差	
设计	黄彬		2020.8.26	单位	mm		>0.5~2	±0.10
审核	张伟		2020.8.26	重量			>2~5	±0.25
批准	罗小春		2020.8.26				>5~10	±0.30
							角度	±0.5°



H	对应高度
0.9	4.3h
1.6	5h
2.1	5.5h
2.6	6h
3.1	6.5h
3.6	7h
4.1	7.5h
4.6	8h
5.1	8.5h
5.6	9h
6.1	9.5h
6.6	10h

第一视角



名称: 轻触开关

型号: HX-6x6x5 TPZJ