









H	
1.5	1.6
1.7	2.0
2.5	3.0
3.5	4.0
4.5	5.0
5.5	



PCB. 焊接图



电 路 图


主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻: $\leq 100\text{m}\Omega$
3. 操 作 力: $250 \pm 50\text{gf}$
4. 行 程: $0.25 \pm 0.10\text{mm}$
5. 绝缘电阻: $\geq 100\text{M}\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 100,000 Cycles

材料:

本体: LCP (灰色)
 按钮: 黄铜 (酸洗)
 卡件: 磷铜 (镀银)
 弹片: 不锈钢 (镀银)
 盖板: 不锈钢
 防水层: 聚酰亚胺

E-mail: hanxiaelectro@126.com

 韩下 HANXIA 深圳市韩下电子有限公司					第一视角 			品名: 轻触开关	
标记	处数	更改文件号	签 名	日 期	比 例	1:1	一般公差		型号: HX 5.2x5.2x1.5H SWITCH TACTILE E-mail:hanxiaswitch@126.com
设 计		黄彬	2021.08.25		单 位	mm	>0.5~2	±0.10	
审 核		张伟	2021.08.28		重 量		>2~5	±0.25	
批 准		罗小春	2021.08.30				>5~10	±0.30	
							角度	±0.5°	