

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G. F UL94V-0, 颜色:黑色.

Housing: PBT+30%G. F UL94V-0, Color: Black

端子: 磷/青铜, 镍底30u"MIN, 表面镀金1u"MIN

Contact: Phosphor bronze, 1u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Rated Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.


Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

IDC3 - XX 2 32 XX A U X 1



NO. OF PINS
6-80P

Contact Plating
Full of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

Contact Plating
Semi-gold

B0=0.8u"

B1=1u"

B2=1.5u"

B3=2u"

B4=3u"

B5=5u"

B6=10u"

B7=15u"

B8=20u"

B9=30u"

INSULATOR
MATERIAL:

A: PBT

Black

Grey427

Grey413

White

Blue

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.			
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2020.12.03	PART NO.	IDC3-XX232XXAUX1		
				X.XXX	±0.10	SHEET	1/1	CHECK		TITLE:	1.27 IDC 塑高3.2 U型 两件式 带凸点		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle	±3°	PROJ.		APPROVE		Customer No.			
				DIM	TOL								