


Specifications



Ordering Information

F185-12 20 A0 A SY E 3

备注 (Remark)
1. 材料 (MATERIAL)
胶芯: PBT+30%G.F UL94V-0, 颜色:黑色.
Housing:PBT+30%G.F UL94V-0, Color:Black
端子: 青铜, 镍底30u"MIN, 表面镀普金
Contact:Bronze, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL
2. 特性 (characteristics):
额定电流: 3 AMP
Raring Current:3 AMP.
接触阻抗: 20 mΩ MAX.
Contact Resistance:20 mΩ MAX.
绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance:1000 MΩ MIN.
耐电压: AC 500V/分钟.
Withstanding Voltage:AC 500V/Minute.
温度范围: -40° C to+105° C
Temperture Range: -40° C to+105° C



NQ OF PINS PER ROW 2~40P	Cont act Pl ating Full Of Gold A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	Señi-gol d B0=0.8U" B1=1U" B2=1.5U" B3=2U" B4=3U" B5=5U" B6=10U" B7=15U" B8=20U" B9=30U"	INSULATOR MATERI AL: A: PBT B: PA6T C: PA9T D: LCP	PACKING A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature				



RoHS
COMPLIANT

注意
事项
1. 带序号为必检尺寸,带*为重点检验尺寸。

				OPERATION		SCALE		Fit		www.yxcon.com 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20	SIZE		A4		DESIGN		PART NO	
				X.XXX	±0.10	SHEET		1/1		CHECK		TITLE	
				Angle	±3°	PROJ.		APPROVE				Customer No.	
				DIM	TOL								
A0	2025.06.11	/	新版发行							李官淼2025.06.11			F185-1220A0ASYE3
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION										2.54排母8.5mm型高 2*20P 180度 PC104 L=10.05 PBT料 镀普金 100/盒