




PC Board Layout

NOTES;

- 1.MATERIAL;
CONTACT;C7701-H T=0.25±0.01mm
2.BURR NOT EXCEED 0.05mm
3.UNLESS OTHERWISE SPECIFIED ALL RADII
ARE 0.15mm MAX
4.PLATING;PLATING NICKEL30U"~80U"
5.STORAGE;-40° C TO +85° C
6.OPERATION;-40° C TO +85° C

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	SFP-101A	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	SFP-101A			X.x	±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx	±0.15
								FILE.NO.	