


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		



NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:3.5*1.5mm热缩套管,黑色	2
②	接头	SSMA母头母针(内孔),直头镀金	2
①	同轴线	RG316棕色线,OD2.5mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO.,LTD.

WWW.KINGHELM.COM.CN
0755-28190160

ALL DIMENSION ARE IN MM	DRAWN James	DATE 2025-3-26	TITLE KH-SSMAK-SSMAK-RG316-100MM		
	CHKD. Frank	2025-3-26			
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	APPD. Scott	2025-3-26			
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150			SIZE DWG Number. B	REV A
CUSTOMER P/N:		SCALE:Free	TYPE	SHEET 1	OF 1