


Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     |      |
|           |        |             |       |     |      |



NOTES:

- ELECTRICAL:
  - VOLTAGE RATING:DCV 300V 10MS
  - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - INSULATION RESISTANCE: 5.0M OHM/MIN.
  - THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
  - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION         | QTY. |
|----------|-------------|---------------------|------|
| ③        | 套管          | OD:3.5*1.5mm热缩套管,黑色 | 2    |
| ②        | 接头          | SSMA母头母针(内孔),直头镀金   | 2    |
| ①        | 同轴线         | RG316棕色线,OD2.5mm    | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO.,LTD.

WWW.KINGHELM.COM.CN  
0755-28190160

|                                                               |                                                                      |                |                                    |              |
|---------------------------------------------------------------|----------------------------------------------------------------------|----------------|------------------------------------|--------------|
| ALL DIMENSION ARE IN MM                                       | DRAWN James                                                          | DATE 2025-3-26 | TITLE<br>KH-SSMAK-SSMAK-RG316-60MM |              |
|                                                               | CHKD. Frank                                                          | 2025-3-26      |                                    |              |
| COMPUTER GENERATED IN SOLIDWORKS<br>DO NOT SCALE THIS DRAWING | APPD. Scott                                                          | 2025-3-26      |                                    |              |
| PROJECTION<br>                                                | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                | SIZE DWG Number.                   | REV A        |
| CUSTOMER P/N:                                                 |                                                                      | SCALE:Free     | TYPE                               | SHEET 1 OF 1 |