


Kinghelm®


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		



NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:3.5*1.5mm热缩套管 黑色	2
②	接头	SSMA公头公针(内针),直头镀金	2
①	同轴线	RG316棕色线,OD2.5mm	AS

深圳市金航标电子有限公司 SHENZHEN KINGHELM ELECTRON CO.,LTD.				WWW.KINGHELM.COM.CN 0755-28190160			
ALL DIMENSION ARE IN MM		DRAWN James		DATE 2025-3-26		TITLE KH-SSMAJ-SSMAJ-RG316-200MM	
		CHKD. Frank		2025-3-26			
COMPUTER GENERATED IN SOLIDWORKS		APPD. Scott		2025-3-26			
DO NOT SCALE THIS DRAWING							
PROJECTION 				SIZE DWG Number.		REV A	
GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150				B		SCALE: Free TYPE	
				SHEET 1		OF 1	