

Specifications

Remark

1. MATERIAL

Housing:PA6T+30%G.F UL94V-0,Color:Black

Contact:Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. characteristics:





Raring Current:1 AMP.

Contact Resistance:20 mΩ MAX.

Insulating Resistance:1000 MΩ MIN.

Withstanding Voltage:AC 500V/Minute.

Temperture Range: -40° C to+105° C



Ordering Information

P310-12 10 A0 B M 062 C 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Semi-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
10: 1.0mm	2-50P	A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	B0=0.8U" B1=1U" B2=1.5U" B3=2U" B4=3U" B5=5U" B6=10U" B7=15U" B8=20U" B9=30U"	B: PA6T C: PA6T D: LCP		A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
		S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature				

				OPERATION		SCALE		Fit		 Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20	SIZE	A4	DESIGN		PART NO.	P310-1210A0BM062C1		
				X.XXX	±0.10								
				Angle	±3°	SHEET	1/1	CHECK		TITLE:			
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.			