


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		



NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:2.5*1.5mm热缩套管,黑色	2
②	接头	SSMA母头母针(内孔),直头镀金	2
①	同轴线	RG178棕色线,OD1.8mm	AS
ALL DIMENSION ARE IN MM		DRAWN James 2025-3-26	DATE
		CHKD. Frank 2025-3-26	DATE
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING		APPD. Scott 2025-3-26	DATE
PROJECTION		TITLE	
GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150		KH-SSMAK-SSMAK-RG178-120MM	
CUSTOMER P/N:		SIZE DWG Number.	
		REV A	
		SCALE:Free	SHEET 1 OF 1