


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		



NOTES:

1. ELECTRICAL:

- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.

2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:2.5*1.5mm热缩套管 黑色	2
②	接头	SSMA公头公针(内针),直头镀金	2
①	同轴线	RG1.37黑色线,OD1.3mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO.,LTD.

WWW.KINGHELM.COM.CN
0755-28190160

ALL DIMENSION ARE IN MM	DRAWN James	DATE 2025-3-26	TITLE KH-SSMAJ-SSMAJ-RG1.37-140MM	
	CHKD. Frank	2025-3-26		
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	APPD. Scott	2025-3-26	SIZE DWG Number.	
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150		B	REV A
SCALE:Free		TYPE	SHEET 1	OF 1

CUSTOMER P/N: