






linear dimension(Tolerances Standard GB/T 14486-2008)								—   		
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to 10	over 10 to 100	over 100 to
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60



PCB LAYOUT



REVISION RECORD				
REV.	DESCRIPTION	ECN No.	APPROVED	DATE
A	新发行		CLF	21.03.16

UL/CUL 技术 参数 UL/CUL Technical Data						
等级	Use Group		B	C	D	
额定电压	Rated Voltage	[V]	600	-	300	
额定电流	Rated Current	[A]	60	-	10	
接线范围	Wire Range		20-6			
单/多芯线	Solid/Stranded	[AWG]				
耐电压	Withstanding Voltage		2200V/1Min			
IEC 技术参数 IEC Technical Data						
过电压类别	Overvoltage Category		III	III	II	
污染等级	Contamination Class		3	2	2	
额定电压	Rated Voltage	[V]	630	1000	1000	
额定电流	Rated Current	[A]	57	57	57	
额定冲击电压	Impulse withstand voltagea	[KV]	8.0	8.0	6.0	
导线截面积	Conductor cross section		10.0			
硬质/柔性导线	Solid/flexible	[mm²]				
材 料 Material						
绝缘材料	Insulation Material		PA66			
阻燃等级	Imflamability		UL94V-0			
导体材料	Contactur Material		铜合金 Copper alloy			
导体表面镀层	Contactive Coating		镀锡 Tin Plated			
一般参数 Other Data						
间距	Pitch	[mm]	10.16			
极数	Poles	[P]	2-24			
剥线长度	Stripping Length	[mm]	10			
螺丝	Screw/扭矩 Torque(Max)	[N.m]	M4.0/1.2			
工作温度	Operating temperatur	[°C]	-40~+105			
引针尺寸	Pin Dimensions	[mm]	5.0			
PCB板孔径	PCB Hole Diameter	[mm]	1.6			

DES.	LQQ	DATE	21.03.16	单位 / UNITS	mm	尺寸 / SIZE	A4	比例 / SCALE	1:1	第三视角 / THIRD ANGLE PROJECTION		版本 / REV	A
CHK.	SY	DATE	21.03.16	 慈溪市科发电子有限公司 CIXI KEFA ELECTRONIC CO., LTD									
APP.	CLF	DATE	21.03.16								名称 / TITLE		KF134C-10.16