



1.FIGURE AND DIMENSIONS(视图及尺寸)



X1511H-XX-N0

XXXXXT-XXXX-XXX-AXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥ ⑦

- ① 系列 (Series No)
- ② Pin位 (Pin bit)
- ③ 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ④ 线规线色 (Wire gauge line color) A: (AWG20-AWG24)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /E(grey)/N (brown)
- ⑤ 线长 (Line length) L: (可定制长度)
- ⑥ 系列 (Series No)
- ⑦ 正反接或镀锡 (Front and reverse or tin-plated) Z(反接)/F (正接) TX (镀锡Xmm)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	Circuit8
Circuit2	黑色	Circuit7
Circuit3	黄色	Circuit6
Circuit4	白色	Circuit5
Circuit5	绿色	Circuit4
Circuit6	蓝色	Circuit3
Circuit7	紫色	Circuit2
Circuit8	灰色	Circuit1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1511H-08-N0	2PCS		
2	X1511T-PSN	16PCS		
3	UL1007/24AWG. 红. 黄. 黑. 绿. 紫. 蓝. 灰. 白色	各1PCS	300MM	
总量				

						DSND		SCALE: N/A	DRAWING NO.		
						DWN		VIEW:	X1511T-08-PSN-A24RBYWGLPE-L300-X1511T-F		
						CHKD		UNIT: mm/in	PART NO.:		
						APPD		SIZE: A4	DWG NO.:		
									WEIGHT	SHEET	REVISION
										1/1	A0

ANGLAR

±5°

Δx

L ≤ 4

±0.2

Δx

4 < L ≤ 16

±0.3

Δx

16 < L ≤ 63

±0.4

MARK

L > 63

±0.5

REVISIONS

UNSPECIFIED TOLERANCES

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

XKB

INDUSTRIAL PRECISION CO.,LIMITED