




REV.	DATE	ECN NO.	MODIFICATION	APPROVER
A	2016/12/20		NEW	Jason
A1	2018/10/11	RD0032018101102	外壳铆合结构变更	Jason



成品加后塞示意图

- Specifications:
- Electrical:
- 1.Current Rating:2.1A/contact terminal
 - 2.Voltage Rating:30V DC
 - 3.Contact Resistance:30 milliohms Max
 - 4.Dielectnic Withstanding Voltage:
500V AC AT Sea Level
 - 5.Insulation Resistance:1000MEGA ohms MIN
- Material:
- 1.Housing:LCP UL94V-0
Color:Black
- Contact:Copper Alloy
- Shell:SUS304
- Finish:
- Contact:Plated Gold in Mating Area;
Tin on Solder Tails
- Shell:Nickel plating



1	VUBS
2	D-
3	D+
4	GND

GENERAL TOLERANCE				UNITS	NAME:		ATOM® 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO.,LTD.			
SELECT	TOL.	1	2	3	MAT'L	PART NO:	TITLE: USB A/F 4P DIP 180° 短体直脚 H=13.7 外壳无翻边			
ON.						USB304FA-B1035206				
X.XXX	±0.15	±0.05	±0.15		FINISH	APPD: JASON	DWG NO. ATOM-A03562			
X.XX	±0.25	±0.13	±0.25		Q'TY	CHKD: VICKY				
X.X	±0.30	±0.25	±0.50			DR: JACK				
X.	±0.38	±0.38	±1.00							
ANGLE	±5°									