









PCB PLERTING PLAN



CIRCUIT DIAGRAM



RoHS
Compliant
2002/95/EC




G-Switch Electronic Technology CO.,Ltd.

Unless otherwise specified, Tolerance:
X. ±0.30
X.x ±0.20
X.xx ±0.15
X.xxx ±0.10
Angles ±3°

DESIGN 陈锋枫 DATE 2016.05.29
CHECKED DATE
APPROVED DATE
<http://www.dg-switch.com>
TEL:0769-82388879

TITLE:
MK-22D14-GXXX 无柱
REV.: X1 SCALE: 4:1 UNIT: mm
SIZE: A4 SHEET: 1/1



MK-22D14-GXXX

侧拨形式

G-SWITCH P/N

G020=2.0mm
G025=2.5mm
G030=3.0mm
G040=4.0mm

G-Switch:

使用温度范围: -20~70℃
耐压: AC250V 50Hz 1min
额定负荷: DC 12V 0.5A
操作力: 200g±100gf
接触电阻: ≤0.05Ω
动作寿命: 10000次
绝缘电阻: ≥100MΩ