






P.C.B. LAYOUT
BOTTOM VIEW



SCHEMATIC (SHOTRING)

SS-23E03-GXXX

直柄 G-Switch P/N

G=020 (2.0) G=030 (3.0)
G=040 (4.0) G=050 (5.0)
G=055 (5.5) G=060 (6.0)
G=065 (6.5) G=070 (7.0)
G=075 (7.5) G=080 (8.0)
G=085 (8.5) G=090 (9.0)
G=095 (9.5) G=100 (10.0)
G=130 (13.0)

G-Switch Specification:
RATING (额定值) : DC250V 0.5A
CONTACT RESISTANCE 接触电阻: $\leq 70\text{m}\Omega$
INSULATION RESISTANCE 绝缘电阻: $\geq 100\text{m}\Omega$
DIELECTRIC STRENGTH 耐电压: AC 500V for 1 minute
TIMING (时间特性) : SHORTING



Unless otherwise specified, Tolerance:
X. ± 0.30
X.x ± 0.20
X.xx ± 0.15
X.xxx ± 0.10
Angles $\pm 3^\circ$

G-Switch Electronic Technology CO.,Ltd.

DESIGN	陈锋枫	DATE	2016.05.29	TITLE: SS-23E03-GXXX					
CHECKED		DATE							
APPROVED		DATE							
http://www.dg-switch.com				REV.:	X1	SCALE:	4:1	UNIT:	mm
TEL:0769-82388879				SIZE:	A4	SHEET:	1/1		