

Rev.	ECN Number	Description	Date	Drawn	Checked	Approved

技术要求:

1.材质:不锈钢SUS301,T=0.10±0.005;

▼ 2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03mm;

3.扭曲:45°/1000mm,拱形 5mm/1000mm;






4.标示有"▼"符号的为重点控制和检验尺寸;

5.未标注之R MAX R0.13;


6.电镀须满足48小时盐雾测试;

7.寿命测试 > 2万次,产品弹力要求在60gf ~ 80gf之间

8.镍底50~80u"min,产品外表面镀金1U"MIN



尺寸公差 ±0.05



GENERAL TOLERANCE				SCALE: 1:1		DRAWN		DWG. NO.		TITLE		REV.
XX. ±0.50				UNIT: mm		CHECK		681-0021A-2		客户图 RF Antenna Spring,SMT, L3.5*W1.5*H2.5mm		A
X. ±0.35						DATE		PARTS NO.(INTENDED USE)				SHEET
.X ±0.25						APPROVE		A-SP-L3.5W1.5H2.5-A				1/1
.XX ±0.15				SIZE: A4		DATE						

MyAntenna