



PowerSSOP-32 to DIP-36 SMT Adapter (0.65 mm pitch, 11 x 6.1 mm)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		6.50				
B		1.50				
C		0.35				
B2		4.11				
C2		3.91				
D		0.30				
D2		1.195				
E		0.65				
F					0.600	
G					0.100	
H					0.025	




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)