






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210686	2021/05/12	Vicky	 X5



Recommended
Panel Cut-Out



-  Note:
- * RoHS Compliant
 - *  Important dimension
 - * Waterproof rate: IPX8, unmated 1m/24h
 - * Connector Housing: Thermoplastic, Black
 - * Pin: Copper alloy, Gold plated
 - * Shield: Metal
 - * Ground: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Green
 - * For panel thickness: 2.0~4.0mm
 - * For pcb thickness max: 1.6mm
 - * Nut is packed separately in pe bag


UNIT:mm		 		TITLE N SEN, M8W/KEY-SHLD, SCREW RECEPTACLE, M, M, PCB R				ITEM NO		DRAWN BY Yulong_wang		DATE 2016-06-14	
TOLERANCE		SCALE 2:1		SIZE A4		SHEET 1 OF 2		DWG NO M8AS-XXPMMR-SF8001		CHECKED BY Jinhai		DATE 2016-06-14	
.X ±0.25		REV. B		WC-REV. A.5		 :Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2016-06-14	
.XX ±0.1													
.XXX ±0.05													
ANGLES ±1°													

Amphenol LTW
安費諾亮泰企業股份有限公司


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


M8AS-XXPMMR-SF8001

XX: No. Of Pin



PCB Layout



Pin Assignments Front View

UNIT:mm		 		TITLE N SEN, M8W/KEY-SHLD, SCREW RECEPTACLE, M, M, PCB R			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO		DRAWN BY Yulong_wang		DATE 2016-06-14	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 2:1								SIZE A4		SHEET 2 OF 2		DWG NO M8AS-XXPMMR-SF8001	
		REV. B		WC-REV. A.5		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2016-06-14			

Amphenol LTW
安費諾亮泰企業股份有限公司