






- | | | | | | | |
|---|-----------|---|-------|---------|--------------------|-------------|
| | YES | 4 & 5 | 31.57 | [1.243] | 8 | 3-647181-8 |
| | YES | 3 & 4 | 23.65 | [.931] | 6 | 3-647181-6 |
| | YES | NONE | 15.72 | [.619] | 4 | 3-647181-4 |
| | | | | | | |
|  | NO | 4 & 5 | 31.57 | [1.243] | 8 | 647181-8 |
|  | NO | 3 & 4 | 23.65 | [.931] | 6 | 647181-6 |
|  | NO | NONE | 15.72 | [.619] | 4 | 647181-4 |
| LEAD | LEAD FREE | BACK WALL
INTERRUPTIONS
BETWEEN POSTS | mm | [IN] | NO OF
POSITIONS | PART NUMBER |
| | | | L | | | |

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. S. HOOVER 22-00CT-0004 CHK. D. BOSSI 22-00CT-0004 APP'D. D. BOSSI 22-00CT-0004		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC # 1 PLC # 2 PLC # 0.13 [.005] 3 PLC # 4 PLC # ANGLE'S FINISH #		NAME ASSEMBLY- MTA .156 HEADER, POLARIZED LOCK, STR .045 SQUARE POST, TIN OR TIN-LEAD PLATED, OMITTED POST #3, SPECIAL	
		PRODUCT SPEC		APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CASE CODE DRAWING NO A1 00779 C-647181	
				RESTRICTED TO	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1 REV F2	