




- 1 TIN PL .000150 MIN THK MIL-T-10727
- 2 PART NO: 324467; .317 LB.
PART NO: 1-324467-0; .317 LB.
PART NO: 2-324467-3; .348 LB.
- 3 .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

1.16	1.41	2.86	△	550-650 MCM	COPPER ASTM-B-75 ANNEALED	2-324467-3
1.16	1.16	2.61	CLEANED △			1-324467-0
			△			324467
"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

DK SCHRUM

4/24/89

CHK

MS FEHER

4/24/89

APVD

WJ VOCKROTH

11/8/89

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

△

CUSTOMER DRAWING

TE Connectivity

SPLICE, BUTT, AMPPOWER
WIRE SIZE: 600 MCM

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=324467

RESTRICTED TO

—

SCALE

2:1

SHEET

1 OF 1

REV

S