






SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!			

Material

● Terminal (housing): Thermoplastic (UL94V-0)

Pitch 5.08

	V8	H5
AS	●	●



SECTION A-A

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

AS xx 00 x 00000G

Color

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

RoHS
Pb<40,000ppm

DIMENSION	Dim D	Dim E	Dim P	Dim L
Dim L =N×5.08+1.9	Poles	Tolerance	Tolerance	Tolerance
Dim P =(N+2)×5.08+0.56	2~6	±0.10	±0.10	±0.15
Dim E =(N+3)×5.08+1.39	7~15	±0.15	±0.15	±0.20
Dim D =(N+4)×5.08+3.3	16~24	±0.20	±0.20	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	AS 5.08mm Series				DWG NO.	8AS0001
PART NO.	ASxx00x00000G			CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance
		Jacke 2009.10.31	Jacke 2009.10.31			X. ±0.50
						X.X ±0.30
						X.XX ±0.10
						X° ±1.5°