

## Coaxial Cable Connector 16\_QLA-01-2-13/122\_N

### Description

Right angle cable plug

Interface standards

NIM-CAMAC-Standard CD/N549



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0046 kg

#### Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Catalogue drawing	DOU-00006830
Assembly instruction	DOC-0000179948

### Ordering Information

Single package	16_QLA-01-2-13/122_NE
----------------	-----------------------

### Additional Information

Suitable cables	G_01130_HT
-----------------	------------