



Pushing Performance
Since 1945

Han 24HPR Enlarged PE Modular Frame A-H



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 024 9933
Specification	Han 24HPR Enlarged PE Modular Frame A-H
HARTING eCatalogue	https://b2b.harting.com/09110249933

Identification

Category	Accessories
Series of hoods/housings	Han [®] HPR enlarged
Type of accessory	Frame
Description of the accessory	for up to 8 single modules A ... H

Version

Size	24 HPR enlarged
Pack contents	1x male PE adapter 1x female PE adapter 2x M3 screw 4x washer SK S6 4x cheese-head screw M6 x 30 4x cheese-head screw M6 x 40

Technical characteristics

Conductor cross-section	4 ... 10 mm ² PE terminal power side 1 ... 2.5 mm ² PE terminal signal side
Tightening torque	0.5 Nm Fixing screws M3 10 Nm Fixing screws M6 0.8 Nm PE terminal clamp 1 ... 2.5 mm ² 1.5 Nm PE terminal clamp 4 ... 10 mm ²
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (accessories)	Zinc die-cast Stainless steel
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	225 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194359
ETIM	EC002310
eCl@ss	27440210 Fixing element for industrial connectors