


# 1N646-1

## FEATURES

- 1N646-1
- SILICON RECTIFIER
- METALLURGICALLY BONDED
- HERMETICALLY SEALED
- DOUBLE PLUG CONSTRUCTION



## MAXIMUM RATINGS AT 25 °C

|                              |                                |
|------------------------------|--------------------------------|
| Operating Temperature:       | -65°C to +175°C                |
| Storage Temperature:         | -65°C to +175°C                |
| Surge Current A, sine 8.3mS: | 5.0A                           |
| Total Power Dissipation:     | 500mW                          |
| Operating Current:           | 400mA, T <sub>A</sub> = +25°C  |
| Operating Current:           | 150mA, T <sub>A</sub> = +150°C |
| Derating Factor:             | 2mA/°C above +25°C             |
| Derating Factor:             | 6mA/°C above +150°C            |
| D.C. Reverse Voltage (VRWM): | 300V                           |

## DC ELECTRICAL CHARACTERISTICS

| V <sub>F</sub> |                   |       |       | I <sub>R</sub> |                       |        |        |
|----------------|-------------------|-------|-------|----------------|-----------------------|--------|--------|
| Ambient (°C)   | I <sub>F</sub> mA | Min V | Max V | Ambient (°C)   | V <sub>R</sub> V (dc) | Min μA | Max μA |
| 25             | 400               | 0.80  | 1.00  | 25             | 300                   | -      | 0.050  |
|                |                   |       |       | 25             | 360                   | -      | 50     |

## DESIGN DATA

**Case:** Hermetically sealed glass package

**Lead Material:** Copper clad steel

**Lead Finish:** Tin/Lead

**Marking:** Blue body coat, Black digits.

**Polarity:** Cathode end is banded.

## AC ELECTRICAL CHARACTERISTICS AT 25°C

|                                   | Symbol | Min | Max |
|-----------------------------------|--------|-----|-----|
| Capacitance @ V <sub>R</sub> = 4V | pF     | -   | 20  |



WWW.MICROSEMI.COM

IRELAND - GORT ROAD, ENNIS, CO. CLARE

PHONE: +353 65 6840044  
TOLL FREE: +186 62 702434  
FAX: +353 65 6822298

U.S.A. DOMESTIC SALES CONTACT

PHONE: (617) 926 0404  
TOLL FREE: 1 800 666 2999