




D

C

B



A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED PER ECR-18-005264	13APR2018	BW	DL




VIEW A-A
SCALE 10:1

- 1 CONTINUOUS STRIP ON REELS.
- 2 CRIMPING INFO:
WIRE BBL-.110 WIDTH,F TYPE
INSUL BBL-.220 WIDTH,O TYPE
- 3 WIRE SIZE TO BE #18-#14 OR TWO #20'S, OR TWO #18'S
- 4 INSULATION RANGE IS .110-.160 OR TWO .105 MAX.
- 5 REREELING FOR 1742109-2



OBSOLETE	TIN	BRASS	1742109-3
	TIN	BRASS	1742109-2
	-	BRASS	1742109-1
	FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON JIANG 31MAY16	 TE Connectivity Ltd.					
		CHK TIM DING 31MAY16						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TIM DING 31MAR16	NAME RECEPTACLE, MINI FASTON,FLAG, .250 SERIES —					
	0 PLC ± —	PRODUCT SPEC 108-5006						
	1 PLC ± —	APPLICATION SPEC 114-2079	SIZE A2	CAGE CODE 00779	DRAWING NO  1742109	RESTRICTED TO —		
	2 PLC ± —							
	3 PLC ± .015							
4 PLC ± —								
ANGLES — ± —								
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT CUSTOMER DRAWING	SCALE 6:1				SHEET 1 of 1	REV A4

D

C

B

A

1742109