


Coaxial Panel Connector 23_BNC-50-0-16/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Number of matings	500
Weight	0.0101 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00010119
Catalogue drawing	DCA-00010121
Mounting hole	DOU-00009051

Ordering Information

Bulk 100 pcs package	23_BNC-50-0-16/133_NH
Single package	23_BNC-50-0-16/133_NE