


- | | | | | | | | |
|-----|----|------|------|----------|------------|----------|------------|
| 111 | 12 | 2 | 2.40 | 1.198 | 1-104257-1 | 12 | 6-103956-1 |
| | 12 | 2 | 2.20 | 1.098 | 1-104257-0 | 1 1 | 6-103956-0 |
| | 12 | 2 | 2.00 | .998 | 104257-9 | 10 | 5-103956-9 |
| | 12 | 2 | 1.80 | .898 | 104257-8 | 9 | 5-103956-8 |
| | 12 | 2 | 1.60 | .798 | 104257-7 | 8 | 5-103956-7 |
| | 12 | 2 | 1.40 | .698 | 104257-6 | 7 | 5-103956-6 |
| | 12 | 4 | 2.39 | .598 | 104257-5 | 6 | 5-103956-5 |
| | 12 | 4 | 1.99 | .498 | 104257-4 | 5 | 5-103956-4 |
| | 12 | 5 | 1.99 | .398 | 104257-3 | 4 | 5-103956-3 |
| | 12 | 8 | 2.40 | .298 | 104257-2 | 3 | 5-103956-2 |
| | 12 | 10 | 2.00 | .198 | 104257-1 | 2 | 5-103956-1 |
| | 10 | 2 | 1.40 | .698 | 104257-6 | 7 | 1-103956-8 |
| | 10 | 2 | 1.60 | .798 | 104257-7 | 8 | 1-103956-7 |
| | 10 | 4 | 2.39 | .598 | 104257-5 | 6 | 1-103956-6 |
| | 10 | 4 | 1.99 | .498 | 104257-4 | 5 | 1-103956-5 |
| | 10 | 5 | 1.99 | .398 | 104257-3 | 4 | 1-103956-4 |
| | 10 | 8 | 2.40 | .298 | 104257-2 | 3 | 1-103956-3 |
| | 10 | 10 | 2.00 | .198 | 104257-1 | 2 | 1-103956-2 |
| | 9 | 2 | 2.40 | 1.198 | 1-104257-1 | 12 | 1-103956-1 |
| | 9 | 2 | 2.20 | 1.098 | 1-104257-0 | 1 1 | 1-103956-0 |
| | 9 | 2 | 2.00 | .998 | 104257-9 | 10 | 103956-9 |
| | 9 | 2 | 1.80 | .898 | 104257-8 | 9 | 103956-8 |
| | 9 | 2 | 1.60 | .798 | 104257-7 | 8 | 103956-7 |
| | 9 | 2 | 1.40 | .698 | 104257-6 | 7 | 103956-6 |
| | 9 | 4 | 2.39 | .598 | 104257-5 | 6 | 103956-5 |
| | 9 | 4 | 1.99 | .498 | 104257-4 | 5 | 103956-4 |
| | 9 | 5 | 1.99 | .398 | 104257-3 | 4 | 103956-3 |
| | 9 | 8 | 2.40 | .298 | 104257-2 | 3 | 103956-2 |
| 9 | 10 | 2.00 | .198 | 104257-1 | 2 | 103956-1 | |

PLATING		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP
---------	---	---	---	---------------------------	------------------	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L A MAYER 11-4-86 CHK P de Jong 11-12-86		 TE Connectivity Ltd.	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± -		NAME RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, LATCHED & POLARIZED, FOR #22-#26 AWG WIRE SIZE, STRIP FORM	
MATERIAL		FINISH SEE TABLE		WEIGHT A2	
HOUSING:		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV P2	