




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.2&3

Pin Assignments




Front View



Conn.1

Pin Assignments


Front View



Conn.3

8	Orange	橘	8	8
7	Yellow	黄	7	7
6	Gray	灰	6	6
5	Red	紅	5	5
4	Green	綠	4	4
3	Blue	藍	3	3
2	White	白	2	2
1	Black	黑	1	1
Conn.1	Wire Color	Conn.2	Conn.3	

Pin Out



- Note:
- * Important Dimension.
 - * Waterproof Rate:IP68.
 - * In 1 meter water within 24 hours.
 - * Connector:Black,PU.
 - * O-Ring:Green,Viton.
 - * Screw Nut:Zinc Alloy,Nickel Plated.
 - * Pin:Copper Alloy,Gold Plated.
 - * Wire Harness:UL1061 26AWG

UNIT:mm		TITLE	M12 Conn T Adaptor
TOLERANCE			MFF Conn MFF Pin,8Pin

SCALE	F ree	SHEET	1	OF	1
REV.	A	SIZE	A4	QC	inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	SS-080808-MFF-TS001	DRAWN BY	H.Z.C.	DATE	2010/05/28
DWG NO	SS-080808-MFF-TS001	CHECKED BY	Dick	DATE	2010/05/28
CUSTOMER	ALTW	APPROVED BY	Luke	DATE	2010/05/28