




D




- △ HOUSING: PBT, UL94V-0, COLOR BLUE.
POSTS: PHOSPHOR BRONZE.
- △ POSTS: 0.00076[.000030] MIN GOLD ON MATING AREA, 0.00254[.000100] MIN TIN ON SOLDER END, ALL OVER 0.00127[.000050] MIN NICKEL ON ENTIRE POST.
- △ DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.
- △ NO KEYING SLOT ON THIS END FOR 6, 10 & 14 POSITION ASSEMBLIES.
- △ NO KEYING SLOT ON THIS END FOR 6 & 10 POSITION ASSEMBLIES.

C



SECTION U-U

B



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

OBSOLETE	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	3-1761680-5
	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	3-1761680-3
	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	3-1761680-1
OBSOLETE	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	2-1761680-9
	27.94 [1.100]	11	35.56 [1.400]	38.10 [1.500]	24	2-1761680-8
	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	2-1761680-7
OBSOLETE	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	2-1761680-6
	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	2-1761680-5
	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	2-1761680-3
OBSOLETE	5.08 [.200]	2	12.70 [.500]	15.24 [.600]	6	2-1761680-1
	D	C	B	A	NO OF POS	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN B. CRISAMORE/DTI 23MAY05
CHK S. BOLASH 23MAY05
APP'D M. WALMSLEY 23MAY05
PRODUCT SPEC
APPLICATION SPEC
SIZE
WEIGHT

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
HEADER ASSEMBLY, RIGHT ANGLE,
LOW PROFILE, IDC
-
SIZE
CAGE CODE
DRAWING NO
RESTRICTED TO

1761680

CUSTOMER DRAWING

SCALE 4:1
SHEET 1 OF 1
REV A

AMP 4805 REV 31MAR2000