

Modular Type Fuse blocks for Class H & J Fuses



Specifications

Description: 3-Pole only, modular type fuse blocks for Class H & J fuses with standard reinforced retaining clips.

Ratings:

- Volts: — 250V (0-60A See Catalog Numbers table)
 — 600V (35-60A See Catalog Numbers table)
- Amps: — 0-60A @ 250Vac/dc (See Catalog Numbers table)
 — 35-60A@600V (See Catalog Numbers table)

SCCR: — Class J 200kA, Class H 10kA

Agency Information: CE, UL Recognized, Guide IZLT2, File E14853, CSA Certified, Class 6225-01, File 47235.

Class H & J Features and Benefits

- H & J modular fuse blocks provide three pole 30 and 60 amp ratings for specific client requirements for separate line and load fuse clip configurations.

Typical Applications

- Up to 60A, space confined, control circuits

Fuse
Holders
& Blocks

Catalog Numbers						
Screw	Pressure Plate	Fuse Class	Volts	Amps	Fig. No.	
11241-3SR*	11241-3PR*	H	250	60	1	
11242-3SR	11242-3PR				2	
11241-3SR	11241-3PR		600	35	1	
11242-3SR**	11242-3PR**				2	
11239-3SR	11239-3PR			60	1	
11240-3SR**	11240-3PR**				2	
11241-3SR	11241-3PR	J		35	1	
11239-3SR*	11239-3PR*			60	1	

Note: Order two blocks per fuse (matched or mixed.)
*11239 and 11241 have wire terminals and mounting holes located under fuse. (Figure 1)
**11240 and 11242 have wire terminals and mounting holes located at end of fuse. (Figure 2)



Figure 1



Figure 2