

Coaxial Panel Connector 22_QLA-01-0-1/112_N

Description

Straight bulkhead receptacle jack

Interface standards

NIM-CAMAC-Standard CD/N549

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Number of matings	10000
Weight	0.0028 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	Nickel Plating
Washer	Bronze	Nickel Plating

Related Documents

Catalogue drawing	DCA-00010163
Mounting hole	DOU-00009337

Ordering Information

Single package	22_QLA-01-0-1/112_NE
Bulk 100 pcs package	22_QLA-01-0-1/112_NH

Remarks

For fastening nut, face spanner 74_Z-0-0-25 is recommended