








LOC	DIST	REVISIONS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		A	INITIAL	05DEC2018	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE) PC BOARD THICKNESS : 1.0~1.6±0.1






AS SHOWN : 1-2348454-0 (20POS: X-KEY) ONLY 4POS --- SEE SHEET 2 OF 3

20	X	9	22.5	26.0	27.6	1-2348454-0
16	X	7	17.5	21.0	22.6	1-2348454-8
12	X	5	12.5	16.0	17.6	1-2348454-6
10	X	4	10.0	13.5	15.1	1-2348454-5
8	X	3	7.5	11.0	12.6	1-2348454-4
6	X	2	5.0	8.5	10.1	1-2348454-3
4	X	1	2.5	6.0	7.6	1-2348454-2
POS	KEY	n	A	B	C	PART NO




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	05DEC2018	TE Connectivity		
		CHK	05DEC2018			
		APVD	05DEC2018			
		PRODUCT SPEC	108-78298			
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5°		NAME 名称 DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS		
		0-PLC ±		SIZE CAGE CODE DRAWING NO 番号 A300779 C-2348454		
		1-PLC ±0.3		RESTRICTED TO		
		2-PLC ±0.10		SCALE 尺度 4:1 SHEET 1 OF 3 REV A		
		3-PLC ±0.001				
		4-PLC ±0.0001				
		ANGLES ±				
MATERIAL 材料 &material		FINISH 仕上 -				
		WEIGHT -				
		RESTRICTED CUSTOMER				

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
© COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1 OF 3		



4POS(X-KEY):1-2348454-2



6POS(X-KEY):1-2348454-3



8POS(X-KEY):1-2348454-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER.ZHU 05DEC2018	 TE Connectivity			
DIMENSIONS: mm		CHK RICK.BIAN 05DEC2018				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RICK.BIAN 05DEC2018	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS			
0 PLC ± 0.3 1 PLC ± 0.10 2 PLC ± 0.10 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES $\pm$		PRODUCT SPEC 108-78298	SIZE A3			
MATERIAL &material		APPLICATION SPEC 114-5377	CAGE CODE 00779			
FINISH -		WEIGHT -	DRAWING NO C-2348454			
RESTRICTED CUSTOMER		RESTRICTED TO		SCALE 4:1		
				SHEET 2 OF 3		
				REV A		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR










DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 3



10POS(X-KEY):1-2348454-5

12POS(X-KEY):1-2348454-6

16POS(X-KEY):1-2348454-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

&material

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3
1 PLC ±0.10
2 PLC ±0.10
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±.

FINISH

-

DWN

FISHER.ZHU

05DEC2018

CHK

RICK.BIAN

05DEC2018

APVD

RICK.BIAN

05DEC2018

PRODUCT SPEC

108-78298

APPLICATION SPEC

114-5377

WEIGHT

-

RESTRICTED CUSTOMER



TE Connectivity

NAME

DYNAMIC D1200D 2.5mmPITCH
HDR ASSY (V-TYPE) TIN PLATING
4-20POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2348454

SCALE

4:1

SHEET

3

OF

3

REV

A