




REVISIONS					
#	LTR	DESCRIPTION	DATE	DWN	APPD
C3		REVISED PER ECO-16-004800	08SEP2016	NK	MZ
D		REVISED PER ECO-17-004657	05APR2017	RS	MZ
E		REVISED PER ECO-18-015685	05OCT2018	RS	MZ

- △ CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- △ RECEPTACLE: NYLON, UL 94V-0 RATED, BLACK.
CONTACT AND POST: BRASS.
SPRING: STAINLESS STEEL.
- △ SOCKET CONTACT AND POST: 2.54um [.000100] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- △ SOCKET CONTACT AND POST: 2.54um [.000100] MIN TIN OVER 1.27um [.000050] MIN NICKEL.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- △ PRELIMINARY PART

9.14 [.360]	△	ALL	1-213928-5
OBsolete	△	B, C, D, E, F, H, I, J, L, M, N	-1-213928-4
OBsolete	△	A, B, C, D, E, F, G, H, K	-1-213928-3
	△	A, B, C, D, E, K	1-213928-2
	△	ALL	1-213928-1
OBsolete	△	B, C, D, E, F, H, I, J, L, M, N	-213928-4
OBsolete	△	A, B, C, D, E, F, G, H, K	-213928-3
OBsolete	△	A, B, C, D, E, K	-213928-2
OBsolete	△	ALL	-213928-1
DIM L	FINISH	POSITIONS LOADED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 31 OCT 95	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 1 NOV 95	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPD R.BRYERS 2 NOV 95	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		RECEPTACLE ASSEMBLY, 20-14, REVERSE SEX, CPC
1 PLC ± -		WEIGHT		
2 PLC ± 0.13 [.005]		SIZE		
3 PLC ± -		CASE CODE		
4 PLC ± -		DRAWING NO		
ANGLES ± -		RESTRICTED TO		A1 00779 C-213928
FINISH		SCALE 4:1		
MATERIAL		SHEET 1 OF 1		REV E
		CUSTOMER DRAWING		