

HDC-CR24-7B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The frames of the modular ConCept system allow ConCept modules to be attached. These frames are designed for sizes 3, 4, 6 and 8. Thus they can be fitted into corresponding enclosures of these sizes.

The fitting capacity of the frames ranges from 2 modules up to 7 modules. This allows the user to put together a custom connector assembly. .

The basic version consists of sturdy, one-piece modules frames available to the user in either polycarbonate or die-cast zinc

Frames are only compatible with each other when they are made of the same material and identical size.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	1682250000
Type	HDC-CR24-7B
GTIN (EAN)	4008 190473983
Qty.	5 pc(s).

HDC-CR24-7B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	111 mm	Depth (inches)	4.37 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	48.6 g		

ConCept Pneumatic module

Colour	black
--------	-------

Dimensions

Height of socket	35 mm	Total length base	111 mm
Width	34 mm		

General data

BG	8	Material	Polyamide, glass fibre-reinforced
Series	ConCept frame	Size	8
Type	Female		

Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	1.2 Nm		

Version

BG	8	Material	Polyamide, glass fibre-reinforced
Size	8		

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-06
ECLASS 9.1	27-44-02-06	ECLASS 10.0	27-44-02-06
ECLASS 11.0	27-44-02-06	ECLASS 12.0	27-44-02-92

Approvals

Approvals



ROHS

Conform

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN