




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	22JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 300V MAX.
- 3
- COLOR: BLUE
- 4
- WIRE RANGE: #22-#14AWG. MAX.3#16 MIN.2#22
- 5
- SPRING INSERT: STEEL

2299501-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 22JAN2016	 TE Connectivity					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK HILL RYAN 22JAN2016	NAME CPGI-WC-WG-BL-BULK					
		APVD HILL RYAN 22JAN2016						
	0 PLC ± - 1 PLC ± 0.2[.007] 2 PLC ± 0.4[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -	SIZE A3			CAGE CODE 00779	DRAWING NO C-2299501	RESTRICTED TO -
		APPLICATION SPEC -						
MATERIAL TOUGH THERMOPLASTIC UL 94V-2 FLAME-RETARDANT	FINISH -	WEIGHT -	CUSTOMER DRAWING					
			SCALE 3:1	SHEET 1 OF 1	REV A			