




NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = 0.4
X.XX = 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
- ▲ 4. CONTACT RATING: 5A @ 250VAC / 8A @ 125VAC
5. CONTACT RESISTANCE: 100mΩ MAX. @ 2-4 VDC
6. ELECTRICAL LIFE: 50,000 CYCLES
- ▲ 7. TRAVEL: 3.0MM
8. CONTACT MATERIAL: COPPER ALLOY WITH SILVER PLATING
9. LAMP VOLTAGE: 6 VDC
10. ▲ CRITICAL PARAMETER
11. 2002/95/EC (ROHS) COMPLIANT



▲ Parts List

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040012	P16OAT11
2	1	F050215	50-002-15 (WHITE LENS TRANSPARENT)
3	1	F051601	P16 TERMINAL PROTECTOR
4	1	F050431	50-004-31 6V LED (WHITE)



TITLE P16OAT11HWHTWHT

A	20121	RELEASE FOR PRODUCTION	8/30/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 8/31/2011

DR BGL

DWG XF0845P

REV A