



DESCRIPTION: M8 FEMALE - PANEL MOUNT (FRONT) - SOLDER CUP - 4 POS.



NOTE:

MATERIAL

HOUSING:

CONTACT:

SHELL

NUT:

O-RING:

FINISH:

CONTACT:

SHELL:

ELECTRICAL

RATED CURRENT:

RATED VOLTAGE:

INSULATION RESISTANCE:

CONTACT RESISTANCE:

WATER PROOF:

ENVIRONMENT

OPERATION TEMPERATURE:

MAX WIRE AWG:

PBT UL94V-0, BLACK

BRASS

BRASS

BRASS

EPDM, BLACK

GOLD PLATED
OVER 50µ" NICKEL
NICKEL

3A

60V

100 MΩhms MIN.

10 mΩhms MAX.


IP67

-40°C TO +85°C


26 AWG

855-A04-203R00Y


1 = GOLD FLASH
4 = 10µ" GOLD



NUT



RECOMMEND PANEL CUT-OUT



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

N.T.S.

SHEET

1

OF

1

REV

3

DWG NO.

855-A04-203R00Y