




| LOC | DIST | REVISIONS |     |                           |         |          |
|-----|------|-----------|-----|---------------------------|---------|----------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN APVD |
| AF  | 50   |           | 0   | TRANSFERED TO TYCO FORMAT | 09JAN03 | MF EH    |

- 1 CRIMPBAND MATERIAL PROVIDED IN CONTINUOUS STRIP.
- 2 REFERENCE DESCRIPTIVE PART NUMBER P051C16B.
- 3 BLANK LENGTH DETERMINED BY 051 TOOLSET.



PARTIAL FORMED VIEW (REF)  
FORMED BY APPLICATION TOOLING

|                                        |  |                                           |  |                                                                                         |  |
|----------------------------------------|--|-------------------------------------------|--|-----------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN 09JAN2003<br>MICHAEL S. FEHER         |  | <b>tyco</b><br>Electronics<br>Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |  |
| CHK 09JAN2003<br>EDWARD HOWARD         |  | APVD 09JAN2003<br>EDWARD HOWARD           |  |                                                                                         |  |
| DIMENSIONS:<br>INCHES                  |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |  | NAME<br>—<br>CRIMPBAND, RTM                                                             |  |
|                                        |  | 0 PLC ± —                                 |  | SIZE                                                                                    |  |
|                                        |  | 1 PLC ± —                                 |  | CAGE CODE                                                                               |  |
|                                        |  | 2 PLC ± —                                 |  | DRAWING NO                                                                              |  |
|                                        |  | 3 PLC ± .005                              |  | RESTRICTED TO                                                                           |  |
|                                        |  | 4 PLC ± —                                 |  | A3 00779 C-1601810                                                                      |  |
|                                        |  | ANGLES ± —                                |  |                                                                                         |  |
| MATERIAL<br>UNS C26000 BRASS           |  | FINISH<br>NONE                            |  | WEIGHT<br>—                                                                             |  |
| CUSTOMER DRAWING                       |  |                                           |  | SCALE 1:1 SHEET 1 OF 1 REV 0                                                            |  |