

D

C

B



A

D


C

B

A



RECOMMENDED PCB LAYOUT



47.5 [1.870]	50.83[2.001]	52.5 [2.067]	20	2-1969730-0
45.0 [1.772]	48.33[1.903]	50.0 [1.968]	19	1-1969730-9
42.5 [1.673]	45.83[1.804]	47.5 [1.870]	18	1-1969730-8
40.0 [1.575]	43.33[1.706]	45.0 [1.772]	17	1-1969730-7
37.5 [1.476]	40.83[1.607]	42.5 [1.673]	16	1-1969730-6
35.0 [1.378]	38.33[1.510]	40.0 [1.575]	15	1-1969730-5
32.5 [1.280]	35.83[1.411]	37.5 [1.476]	14	1-1969730-4
30.0 [1.181]	33.33[1.312]	35.0 [1.378]	13	1-1969730-3
27.5 [1.083]	30.83[1.214]	32.5 [1.280]	12	1-1969730-2
25.0 [.984]	28.33[1.115]	30.0 [1.181]	11	1-1969730-1
22.5 [.886]	25.83[1.016]	27.5 [1.083]	10	1-1969730-0
20.0 [.787]	23.33[.919]	25.0 [.984]	9	1969730-9
17.5 [.689]	20.83[.820]	22.5 [.886]	8	1969730-8
15.0 [.591]	18.33[.722]	20.0 [.787]	7	1969730-7
12.5 [.492]	15.83[.623]	17.5 [.689]	6	1969730-6
10.0 [.395]	13.33[.525]	15.0 [.591]	5	1969730-5
7.5 [.295]	10.83[.426]	12.5 [.492]	4	1969730-4
5.0 [.197]	8.33[.328]	10.0 [.395]	3	1969730-3
2.5 [.098]	5.83[.229]	7.5 [.295]	2	1969730-2
DIM C		DIM B	DIM A	POS PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm[INCHES]

MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.30
1 PLC ±.20
2 PLC ±.20
3 PLC ±.
4 PLC ±.
ANGLES ±3°
FINISH -
-

DWN 04JUN2016 NAGALAKSHMI K
CHK 04JUN2016 CHIARELLI DAVIDE
APVD 04JUN2016 CHIARELLI DAVIDE

PRODUCT SPEC
108-2418
APPLICATION SPEC
114-13315
WEIGHT -
CUSTOMER DRAWING

TE Connectivity

NAME
HEADER ASSEMBLY, VERTICAL, ECONOMY POWER, 2.5mm CENTERLINE
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1969730

RESTRICTED TO
-

SCALE
4:1

SHEET
2

OF
2

REV
A3

1471-9 (3/13)