


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-15-010519	20JUN2015	DW	CW
	A2	ECR-16-010326	07JUL2016	DW	CW
	A3	ECR-16-018349	30DEC2016	DW	CW
	B	ECR-21-108563	28JUL2021	WOR	CW



NOTES:
I. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
HOOD SURFACE: CONDUCTIVE PAINTING
HOOD SURFACE COLOR: TRANSPARENCY
HOOD RESISTANCE: $\leq 10 \text{ m}\Omega$
DEGREE OF PROTECTION: IP65 (MATED)

注 释:

1. 技术参数:

上壳材料: 铝合金

上壳表面处理: 喷导电漆

上壳表面处理颜色: 透明

上壳电阻: $\leq 10\text{ m}\Omega$

防护等级: IP65 (配合)



T1270245121-000	H24B-TSBHS-EMC-PG21	H24B EMC HOOD,SIDE ENTRY PG21,STAINLESS STEEL DOUBLE LOCKING,HIGH CONSTRUCTION H24B屏蔽上壳,侧出PG21,不锈钢双扣,高结构	PG21
T1270245129-000	H24B-TSBHS-EMC-PG29	H24B EMC HOOD,SIDE ENTRY PG29,STAINLESS STEEL DOUBLE LOCKING,HIGH CONSTRUCTION H24B屏蔽上壳,侧出PG29,不锈钢双扣,高结构	PG29
T1270245125-000	H24B-TSBHS-EMC-M25	H24B EMC HOOD,SIDE ENTRY M25,STAINLESS STEEL DOUBLE LOCKING,HIGH CONSTRUCTION H24B屏蔽上壳,侧出M25,不锈钢双扣,高结构	M25
T1270245132-000	H24B-TSBHS-EMC-M32	H24B EMC HOOD,SIDE ENTRY M32,STAINLESS STEEL DOUBLE LOCKING,HIGH CONSTRUCTION H24B屏蔽上壳,侧出M32,不锈钢双扣,高结构	M32
T1270245140-000	H24B-TSBHS-EMC-M40	H24B EMC HOOD,SIDE ENTRY M40,STAINLESS STEEL DOUBLE LOCKING,HIGH CONSTRUCTION H24B屏蔽上壳,侧出M40,不锈钢双扣,高结构	M40
PART NUMBER 零件料号	PART DESCRIPTION 零件描述		PG/M THREAD PG/M 螺纹孔

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10JUL2014 CHK DAVID WANG CHRIS WANG APVD 10JUL2014 XIANG XU PRODUCT SPEC 108-137016 APPLICATION SPEC 114-137016 WEIGHT - Customer Drawing		 TE Connectivity NAME H24B-TSBHS-EMC-PG/M SIZE A2		CAGE CODE 00779		DRAWING NO C-T12702451XX000		RESTRICTED TO -	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		SCALE 1:1		SHEET 1 OF 1		REV B		MATERIAL - -	