

Han-Eco 10B Outd-HBM-with SL



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 210 0340
Specification	Han-Eco 10B Outd-HBM-with SL
HARTING eCatalogue	https://b2b.harting.com/19432100340

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco [®] B
Type of hood/housing	Bulkhead mounted housing

Version

Size	10 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94
(locking levers)

V-0

RoHS	compliant
------	-----------

ELV status	compliant
------------	-----------

China RoHS	e
------------	---

REACH Annex XVII substances	Not contained
-----------------------------	---------------

REACH ANNEX XIV substances	Not contained
----------------------------	---------------

REACH SVHC substances	Not contained
-----------------------	---------------

California Proposition 65 substances	Yes
--------------------------------------	-----

Fire protection on railway vehicles	EN 45545-2 (2020-08)
-------------------------------------	----------------------

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 Fire protection on railway vehicles

Approvals	CE
-----------	----

Commercial data

Packaging size	1
----------------	---

Net weight	116 g
------------	-------

Country of origin	Germany
-------------------	---------

European customs tariff number	85389099
--------------------------------	----------

GTIN	5713140178205
------	---------------

ETIM	EC000437
------	----------

eCl@ss	27440202 Shell for industrial connectors
--------	--