

Between Series Adaptor 31_N-SMB-50-1/1--_U

Description

Adaptor jack/jack
N jack (female) / SMB jack (female)

Interface standards

Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210

Series SMB - IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 3 GHz ≤ 1.03 + 0.08 f (GHz)
Frequency range	3 to 4 GHz
Return loss	≥ 18 dB

Mechanical Data

Number of matings	500
Weight	0.0203 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - SMB jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014586
-------------------	--------------

Ordering Information

Single package	31_N-SMB-50-1/1--_UE
----------------	----------------------