

## MATERIAL:

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

GOLD PLATED BRASS

(SEE P/N KEY BELOW)

NUT:

NICKEL PLATED BRASS

SHELL:

NICKEL PLATED BRASS

O-RING:

EPDM, BLACK

## ELECTRICAL:

RATED CURRENT:

4A

RATED VOLTAGE:

250V

INSULATION RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 mOhms MAX.



## ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C



WATER PROOF: IP67

MAX WIRE AWG:

20



NUT



## NORCOMP MATING PART NUMBERS:

858-003-103RLU4\*

859-003-103R004\*

860-L03-113R004\*

861-003-113R004\*

\*Also all material and contact plating variants

858-003-203RLSY

3 = BRASS/NICKEL (B/N) SHELL & NUT  
 S = STAINLESS STEEL (SS) SHELL & NUT  
 T = B/N SHELL / SS NUT

1 = GOLD FLASH  
 4 = 10 $\mu$ " GOLD

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03/07/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

| SCALE:  | 1 | OF | 1 | REV |
|---------|---|----|---|-----|
| NTS     |   |    |   | 6   |
| DWG NO. |   |    |   |     |
|         |   |    |   |     |

858-003-203RLSY