


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-18-002683	23FEB2018	FV	TD



THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT - By -

STOCK THK.

0.41 [.016] THK.

WIRE RANGE

20-16

INSUL RANGE

1.5-2.13 [.059-.084]

TIN PLATE

PHOS. BRONZE

154740-2

NONE

PHOS. BRONZE

154740-1

FINISH

MATERIAL

PART NUMBER

DIMENSIONS:

mm [INCHES]

DWN

RAVI S

04JAN2017

CHK

LI DAISY

04JAN2017

APVD

DING TIM

04JAN2017

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

MATERIAL

SEE TABLE

FINISH

SEE TABLE

TE

TE Connectivity

NAME

.177 (4.50) DIA. RIGHT ANGLE PIN RECEPTACLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-154740

—

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV A1